



Paskirstytojas

NEDY-L2R1-V1-Z4W2Z-U-0.3L-M12G4-2.5R

Gaminio numeris: 8035787

FESTO



Tech. Duomenys

Savybės	Reikšmė
Paremtas standartu	EN 61076-2-101
Leidimas	RCM Mark
Konstrukcija	Y-distributor with cables on both sides
Distributor type	2 to 1
Signal status display	LED geltonas
Papildomos funkcijos	Laikymo srovės sumažėjimas
Cable identification	With inscription label holder
Montavimo tipas	With through-hole for M2 screw su priedais
Produkto svoris	90 g
Electrical connection 1, function	Controller side
Electrical connection 1, design	apvalus
Electrical connection 1, connection type	Kištukas
Electrical connection 1, cable outlet	Tiesus
Electrical connection 1, connection technology	M12x1, A-coded in accordance with EN 61076-2-101
Electrical connection 1, number of pins/wires	4
Electrical connection 1, occupied pins/wires	3
Electrical connection 2, function	Field device side
Electrical connection 2, design	kampinis
Electrical connection 2, connection type	2x rozetė
Electrical connection 2, cable outlet	Angled
Electrical connection 2, connection technology	Connection pattern ZC, metric screw
Electrical connection 2, number of pins/wires	2
Electrical connection 2, occupied pins/wires	2
Nominalus DC įtampos lygis	20,4 ... 27,6 V
Leistina srovės apkrova prie 40°C	1 A
Atsparumas smūgiams	0,8 kV
Cable length 1	2,5 m
Cable length 2	0,3 m
Kabelio priedas	Suitable for energy chains/robot applications
Note on cable characteristics	Field device side: standard
Laido bandymo sąlygos	Atsparumas lenkimui pagal Festo normas, bandymo sąlygos pagal užklausimą. Bandytas pagal užklausimą Atsparumas sukimui: > 300 000 Zyklen, ±270°/0,1 m Energy chain: > 5 million cycles, bending radius 28 mm
Note on cable test conditions	For standard cables: Energy chain: 1.5 million cycles, bending radius 75 mm, resistance to bending: to Festo standard, test conditions on request
Minimum bending radius with freely moveable use 1	39 mm
Minimum bending radius with freely moveable use 2	30 mm
Cable diameter 1	3,8 mm
Cable diameter 2	2,9 mm
Nominalus laidininko skerspjūvis	0,25 mm ²
Apsaugos klasė	IP65
Aplinkos temperatūra	-10 ... 50 °C
Note on ambient temperature	-10 ... 40 °C when mounted via through-hole

Savybės	Reikšmė
Aplinkos temperatūra esant lankščiai kabelių instaliacijai	-5 ... 50 °C
Saugojimo temperatūra	-10 ... 50 °C
CE ženklas (žr. deklaraciją)	atitinka EU-EMV reikalvumus in accordance with EU RoHS directive
UKCA marking (see declaration of conformity)	To UK instructions for EMC To UK RoHS instructions
PWIS conformity	VDMA24364-B2-L
Informacija	atitinka RoHS
Užterštumo laipsnis	3
Atsparumo korozijai klasė CRC	2 - Moderate corrosion stress
Material cable sheath	TPE-U(PUR)
Kabelio apvalkalo spalva	pilkas
Material housing	PA TPE-U(PUR)
Korpuso spalva	Juodas
Material seals	NBR TPE-O
Material electrical contact	Gold-plated copper alloy Copper alloy, tinned
Material threaded sleeve	Nikeliuotas varis