

Jungtis su kabeliu NEBU-M12W8-K-15-N-LE8

Gaminio numeris: 8048086

FESTO



Tech. Duomenys

Savybės	Reikšmė
Atitinka standartus	EN 61076-2-101
Cable identification	Without inscription label holder
Produkto svoris	848 g
Electrical connection 1, function	Field device side
Electrical connection 1, design	apvalus
Electrical connection 1, connection type	Kištuko lizdas
Electrical connection 1, cable outlet	Angled
Electrical connection 1, connection technology	M12x1, A-coded in accordance with EN 61076-2-101
Electrical connection 1, number of pins/wires	8
Electrical connection 1, occupied pins/wires	8
Electrical connection 1, type of mounting	Screw lock
Electrical connection 2, function	Controller side
Electrical connection 2, connection type	Kabelis
Electrical connection 2, connection technology	atviri laidai
Electrical connection 2, number of pins/wires	8
Electrical connection 2, occupied pins/wires	8
Nominalus DC įtampos lygis	0 ... 30 V
Nominalus AC įtampos lygis	0 ... 30 V
Leistina srovės apkrova prie 40°C	2 A
Atsparumas smūgiams	0,8 kV
Kabelio ilgis	15 m
Kabelio priedas	Standartas
Bending radius, fixed cable installation	≥ 32 mm
Bending radius, flexible cable installation	≥ 66 mm
Kabelio skersmuo	6,3 mm
Kabelio skersmens tolerancija	± 0,2 mm
Kabelio struktūra	8x0,25 Ekranuotas
Nominalus laidininko skerspjūvis	0,25 mm ²
Laido galai	Galvanizuota
Apsaugos klasė	IP67
Note on degree of protection	Sumontuotas
Aplinkos temperatūra	-25 ... 80 °C
Aplinkos temperatūra esant lankščiai kabelių instaliacijai	-5 ... 80 °C
CE ženklas (žr. deklaraciją)	in accordance with EU RoHS directive
UKCA marking (see declaration of conformity)	To UK RoHS instructions
PWIS conformity	VDMA24364-B2-L
Informacija	atitinka RoHS
Užterštumo laipsnis	3
Atsparumo korozijai klasė CRC	2 - Moderate corrosion stress
Material cable sheath	TPE-U(PUR)
Kabelio apvalkalo spalva	pilkas
Material housing	TPE-U(PUR)
Material of union nut	Nikeliuotas varis
Material seals	NBR
Material electrical contact	Brass, gold-plated
Material insulation	PP