

Pasyvi ašių kreipiančioji ELFC-KF-80-1800

Gaminio numeris: 8062834

FESTO



Tech. Duomenys

| Savybės | Reikšmė |
|--|--|
| Darbinė eiga | 1.800 mm |
| Dydis | 80 |
| Eigos rezervas | 0 mm |
| Montavimo pozicija | Bet koks |
| Kreipiančioji | Cirkuliuojantis guolio kreipiklis |
| Konstrukcija | Kreipiamoji |
| Maksimalus pagreitis | 500 m/s ² |
| Maksimalus greitis | 1,5 m/s |
| Budėjimo ciklas | 100 % |
| Atsparumo korozijai klasė CRC | 0 - No corrosion stress |
| PWIS conformity | VDMA24364 zone III |
| RSBP classification to CD-0033 | F1a |
| Švaros klasė | ISO class 7 |
| Apsaugos klasė | IP40 |
| Aplinkos temperatūra | 0 ... 50 °C |
| Inercijos momentas I _y | 1.370E+03 mm ⁴ |
| Inercijos momentas I _z | 1.660E+03 mm ⁴ |
| Maksimali jėga F _y | 900 N |
| Maksimali jėga F _z | 2.700 N |
| Maksimalus momentas M _x | 59,8 Nm |
| Maksimalus momentas M _y | 56,2 Nm |
| Maksimalus momentas M _z | 56,2 Nm |
| Susukimo inercijos momentas I _t | 90,5E+03 mm ⁴ |
| Perstūmimo jėga | 15 N |
| F _y with theoretical service life of 100 km (from a guide perspective only) | 3.312 N |
| F _z with theoretical service life of 100 km (from a guide perspective only) | 9.936 N |
| M _x with theoretical service life of 100 km (from a guide perspective only) | 220 Nm |
| M _y with theoretical service life of 100 km (from a guide perspective only) | 207 Nm |
| M _z with theoretical service life of 100 km (from a guide perspective only) | 207 Nm |
| Judanti masė | 815 g |
| Papildomas svoris 10mm ilgiui | 73 g |
| Material of end caps | Die-cast aluminium, painted |
| Material of profile | Anodised wrought aluminium alloy |
| Informacija | atitinka RoHS |
| Material cover tape | aukštai legiruotas plienas, nerūdijantis |
| Material cover | Die-cast aluminium, painted |
| Material guide slide | Plienas |
| Material guide rail | Plienas |
| Material slide | Padengtas aliuminiu |