

Plastikiniai vamzdeliai

PTFEN-5/32-NT-300

Gaminio numeris: 8063350

FESTO



Tech. Duomenys

Savybės	Reikšmė
Išorinis diametras	3,97 mm
Lenkimo spindulys atitinkantis srautą	32 mm
Vidinis diametras	2,9 mm
Min. lenkimo spindulys	32 mm
Instructions for use	Tubing without printing
Operating pressure for entire temperature range	-0,095 ... 0,5 MPa
Darbiis slėgis visam temperatūros diapozonui.	-0,95 ... 5 bar
Operating pressure for entire temperature range	-13,775 ... 72,5 psi
Temperature-dependent operating pressure	-0,095 ... 1,2 MPa
Temperatūros priklausomybė nuo darbinio slėgio	-0,95 ... 12 bar
Temperature-dependent operating pressure	-13,775 ... 174 psi
Darbinė terpė	Suslėgto oro kokybė pagal ISO8573-1:2010 [7:-:-]
Material fire test	UL94 V-0
PWIS conformity	VDMA24364-B1/B2-L
Švaros klasė	This product is a static object, active particle generation is not possible when used correctly. Clean product before using it in a cleanroom environment and ensure it is installed correctly.
Food-safe	See Supplementary material information
Aplinkos temperatūra	-20 ... 150 °C
Produkto svoris pagal ilgį	0,013 kg/m
Pneumatinis pajungimas	For push-in connector outside diameter 5/32"
Spalva	bespalvis
Atramos kietumas	D 55 +/-5
Informacija	atitinka RoHS
Material tubing	PTFE