

Power supply plug NECL-S-L12W5-C2-Q10

Gaminio numeris: 8166792

FESTO



Tech. Duomenys

| Savybės | Reikšmė |
|--|---|
| Paremtas standartu | EN 61076-2-111 |
| Leidimas | c UL us - Recognized (OL) |
| Skyriaus sertifikatas | UL E474609 |
| Montavimo tipas | Threaded |
| Cable outlet | Angled |
| Note on cable outlet | Can be rotated 72° |
| Produkto svoris | 45,69 g |
| Electrical connection 1, function | Maitinimas |
| Electrical connection 1, design | apvalus |
| Electrical connection 1, connection type | Kištukas |
| Electrical connection 1, connection technology | M12x1, L-coded to EN 61076-2-111 |
| Electrical connection 1, number of pins/wires | 5 |
| Electrical connection 2, connection technology | Įsuktas terminalas |
| Nominalus DC įtampas lygis | 0 ... 63 V |
| Nominali darbinė nuolatinė įtampa | 63 V |
| Leistina srovės apkrova prie 40°C | 16 A |
| Atsparumas smūgiams | 1,5 kV |
| Leistinas kabelio skersmuo | 8 - 13 mm for electrical connection 1 |
| Nominalus laidininko skerspjūvis | ≤ 2,5 mm ² |
| Nominal conductor cross section (AWG) | AWG14 |
| Nuoroda į pajungimo skerspjūvį | Max. 1.5 mm ² /AWG16 when using wire end sleeves |
| Apsaugos klasė | IP65 IP67 |
| Aplinkos temperatūra | -40 ... 105 °C |
| PWIS conformity | VDMA24364-B2-L |
| Informacija | atitinka RoHS |
| Užterštumo laipsnis | 3 |
| Atsparumo korozijai klasė CRC | 1 - Low corrosion stress |
| Material housing | PA |
| Material screw-type lock | Nickel-plated die-cast zinc |
| Material electrical contact | Gold-plated copper alloy |