

# Ventuza VAS-125-3/8-PUR

Cod: 152606

FESTO

cu inel de etansare OL.



## Fisa tehnica

Caracteristica	valoare
deschidere nominala	7 mm
diametru ventuza	125 mm
diametru efectiv ventuza	125 mm
structura constructiva	racord de vacuum deschis rotund, standard
mediu de operare	aer atmosferic
temperatura mediului	-20 ... 60 °C
forta de rupere la 70% vacuum	606 N
filet de fixare	G3/8
fixarea ventuzei	G3/8
racord de vacuum	G3/8
duritate Shore	62
informatii referitoare la material pentru fus cu insurubare	aliaj maleabil aluminiu
informatii referitoare la material pentru ventuza	TPE-U(PU)