

Dopuri opturare QSMC-1/8H-U

Cod: 153924

FESTO

Acest produs este disponibil doar de la Festo Gesellschaft SUA.
Type to be discontinued. Available until 2013. See Support Portal
for alternative products.



Fisa tehnica

Caracteristica	valoare
pozitie instalare	oricare
marimea legaturii	1
structura constructiva	principiu Push-Pull
Operating pressure complete temperature range	-0,95 ... 10 bar
mediu de operare	Compressed air in accordance with ISO8573-1:2010 [7:-:-]
Note on operating and pilot medium	Lubricated operation possible
clasa de rezistenta la coroziune KBK	1
temperatura mediului	-10 ... 60 °C
aprobare	Germanischer Lloyd
greutate produs	0,5 g
racord pneumatic 1	Push-in sleeve QS-1/8"
indicatie material	conform RoHS
informatii referitoare la material pentru carcasa	PBT