

Amorizor de zgomot U-M3

Cod: 163978

★ Standard-Programm

Produs in retragere de pe piata

Type to be discontinued. Do not use for new projects. See Support Portal for alternative products.

FESTO



Fisa tehnica

Caracteristica	valoare
pozitie instalare	oricare
presiune de operare	0 ... 10 bar
mediu de operare	Compressed air in accordance with ISO8573-1:2010 [7:-:-]
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
nivel presiune zgomot	65 dB(A)
temperatura mediului	-10 ... 70 °C
racord pneumatic	M3
informatii referitoare la material pentru kit instalare amortizoare	bronz
informatii referitoare la material pentru fus cu insurubare	alama
indicatie material	conform RoHS