


Ventuza burduf VASB-8-M5-NBR-CT

Cod: 183514

FESTO

cu inel de etansare OL.

Tip iesit din fabricatie. Livrabil pana in 2010.



Fisa tehnica

Caracteristica	valoare
deschidere nominala	2 mm
diametru ventuza	8 mm
diametru efectiv ventuza	5,5 mm
structura constructiva	racord de vacuum deschis rotund, burduf incretit de 1,5 ori
mediu de operare	aer atmosferic
temperatura mediului	-20 ... 80 °C
forta de rupere la 70% vacuum	1,6 N
filet de fixare	M5
fixarea ventuzei	M5
racord de vacuum	M5
duritate Shore	73
indicatie material	Fara cupru si PTFE
informatii referitoare la material pentru ventuza	TPE-U(PU)