



Fisa tehnica

Caracteristica	valoare
marime de fabricatie	standard
deschidere nominala	10 mm
Operating pressure complete temperature range	-0,95 ... 16 bar
mediu de operare	Compressed air in accordance with ISO8573-1:2010 [7:-:-]
Note on operating and pilot medium	Lubricated operation possible
clasa de rezistenta la coroziune KBK	3
Food safety	to manufacturer's declaration
temperatura mediului	0 ... 150 °C
aprobare	Germanischer Lloyd
greutate produs	14,1 g
racord pneumatic 1	Racord de imbinare QS-12
indicatie material	conform RoHS
informatii referitoare la material pentru carcasa	alama cromat si nichelat