


Regleta de conectare. VABM-B6-E-G12-4

Cod: 537507

FESTO

pentru electroventil VUVB.



Fisa tehnica

Caracteristica	valoare
marimea ramei	21 mm
numarul max. de pozitii de ventile	4
clasa de rezistenta la coroziune KBK	2
Moment de strangere max., montaj sina H	1,5 Nm
moment maxim de strangere la fixarea ventilului	2 Nm
Moment de strangere max., montaj perete	5 Nm
greutate produs	690 g
racord aer auxiliar de comanda 12/14	G1/8
racord pneumatic 1	G1/2
racord pneumatic 3	G1/2
indicatie material	Fara cupru si PFTE conform RoHS
Informatie material bara racordare	aliaj maleabil aluminiu