


racord cu fisa
QS-F-14
Cod: 570432

FESTO



Fisa tehnica

Caracteristica	valoare
marime de fabricatie	standard
deschidere nominala	13 mm
structura constructiva	principiu Push-Pull
Operating pressure complete temperature range	-0,95 ... 16 bar
mediu de operare	Compressed air in accordance with ISO8573-1:2010 [7:-:-]
Note on operating and pilot medium	Lubricated operation possible
clasa de rezistenta la coroziune KBK	3
Food safety	to manufacturer's declaration
temperatura mediului	0 ... 150 °C
aprobare	Germanischer Lloyd
greutate produs	73 g
racord pneumatic 1	Push-in sleeve QS-14
racord pneumatic 2	Push-in sleeve QS-14
indicatie material	conform RoHS
informatii referitoare la material pentru carcasa	alama cromat si nichelat
informatii referitoare la material pentru etansare furtun	FPM