

Dopuri opturare QSC-F-14H

Cod: 570444

FESTO



Fisa tehnica

| Caracteristica | valoare |
|---|--|
| marime de fabricatie | standard |
| Operating pressure complete temperature range | -0,95 ... 16 bar |
| mediu de operare | Compressed air in accordance with ISO8573-1:2010 [7:-:-] |
| Note on operating and pilot medium | Lubricated operation possible |
| clasa de rezistenta la coroziune KBK | 3 |
| Food safety | to manufacturer's declaration |
| temperatura mediului | 0 ... 150 °C |
| aprobare | Germanischer Lloyd |
| greutate produs | 20 g |
| racord pneumatic 1 | Push-in sleeve QS-14 |
| indicatie material | conform RoHS |
| informatii referitoare la material pentru carcasa | alama cromat si nichelat |