


Bobina

VACC-S18-35-K4-1UF-EX4ME

Cod: 8109388

FESTO



Fisa tehnica

Caracteristica	valoare
tip de actionare	electric
pozitie instalare	Oricare
Afisarea pozitiei de comutare	nu
Protectie interna	Siguranta de protectie
Durata de anclansare	100 %
Clasa izolatie	H
Caracteristica bobina	24 V DC: 3.5 W 24 V AC: 50/60 Hz, putere 3,5 VA
Oscilatii admisibile ale tensiunii	-15 % / +10 %
Simbol CE (vezi declaratia de conformitate)	conform directivei europene de protectie Ex (ATEX)
Marcaj UKCA (a se vedea declaratia de conformitate)	conform reglementarilor UK EX
Certificat ATEX in afara UE	EPL Db (GB) EPL Db (IEC-EX) EPL Gb (GB) EPL Gb (IEC-EX)
Departament eliberare certificate	BVS 16ATEXE036X IECEX BVS16.0028X
Gaz categoria ATEX	II 2G
Praf categoria ATEX	II 2D
Tip gaz cu protectie la explozie si aprindere	Ex eb mb IIC T6, T5 Gb
Tip praf cu protectie la aprindere si explozie	Ex tb IIIC T80°C, T95°C Db
Protectie la explozie temperatura ambientala	T5,T95°C: -25°C ≤ Ta ≤ +60°C T6,T80°C: -25°C ≤ Ta ≤ +50°C
Conformitatea PWIS	VDMA24364-zona III
Tip de protectie	IP66
Greutate produs	580 g
Conectare electrica	Cutie terminal, cablu filetat M20x1.5
Indicatie material	conform RoHS