

# Bobina VACC-S18-35-K4-1UF-NE4ME

Cod: 8118256

FESTO



## Fisa tehnica

| Caracteristica                                 | valoare  |
|--|--|
| tip de actionare                               | electric   |
| pozitie instalare                              | Oricare  |
| Afisarea pozitiei de comutare                  | nu   |
| Protectie interna                              | Siguranta de protectie                                       |
| Durata de anclansare                           | 100 %  |
| Clasa izolatie                                 | H  |
| Caracteristica bobina                          | 24 V DC: 3.5 W<br>24 V AC: 50/60 Hz, putere 3,5 VA           |
| Oscilatii admisibile ale tensiunii             | -15 % / +10 %  |
| Certificat ATEX in afara UE                    | EPL Db (CN)<br>EPL Gb (CN)                                   |
| Departament eliberare certificate              | GYJ17.1237X  |
| Tip gaz cu protectie la explozie si aprindere  | Ex e mb IIC T5/T6 Gb   |
| Tip praf cu protectie la aprindere si explozie | Ex tD A21 IP66 T95°C/T80°C                                   |
| Protectie la explozie temperatura ambientala   | T5,T95°C: -25°C ≤ Ta ≤ +60°C<br>T6,T80°C: -25°C ≤ Ta ≤ +50°C |
| Conformitatea PWIS                             | VDMA24364-zona III   |
| Tip de protectie                               | IP66   |
| Greutate produs                                | 580 g  |
| Conectare electrica                            | Cutie terminal, cablu filetat M20x1.5                        |
| Indicatie material                             | conform RoHS   |