


Reductor EMGA-60-A-G8-60P

Cod: 8141738

FESTO



Fisa tehnica

Caracteristica	valoare
Transmisie flansa	60 mm
Motor cu flansa	60 mm
Joc de rasucire	0,27 deg
tipul reductorului	Reductor in unghi drept
Raport de transmisie	8:1
Viteza maxima de intrare	13.000 1/min
Temperatura de operare reductor	-25 ... 90 °C
Conformitatea PWIS	VDMA24364-B2-L
Tip de protectie	IP54
Cuplu de actionare continua	18 Nm
Momentul de inertie al angrenajului	0,243 kgcm ²
Cuplu maxim iesire	29 Nm
Eficienta maxima	93 %
rigiditate la torsiune	1,6 Nm/arcmin
Greutate produs	1.700 g
Interfata reductor arbore de iesire	60G
Interfata reductor arbore de antrenare	60P
Indicatie material	conform RoHS