

Reductor EMGA-80-P-G12-SST-87

Cod: 8141767

FESTO



Fisa tehnica

Caracteristica	valoare
Transmisie flansa	80 mm
Motor cu flansa	87 mm
Joc de rasucire	0,15 deg
tipul reductorului	Angrenaj planetar
Raport de transmisie	12:1
Viteza maxima de intrare	7.000 1/min
Temperatura de operare reductor	-25 ... 90 °C
Conformitatea PWIS	VDMA24364-B2-L
Tip de protectie	IP54
Cuplu de actionare continua	120 Nm
Momentul de inertie al angrenajului	0,589 kgcm ²
Cuplu maxim iesire	192 Nm
Eficienta maxima	97 %
rigiditate la torsiune	10,4 Nm/arcmin
Greutate produs	2.600 g
Interfata reductor arbore de iesire	80G
Interfata reductor arbore de antrenare	87A
Indicatie material	conform RoHS