

Protectie la exhaustare VABD-D3-L-GN12

Cod: 8177961

FESTO



Fisa tehnica

Caracteristica	valoare
pozitie instalare	Oricare
Presiune de operare Mpa	0 ... 1,2 MPa
presiune de operare	0 ... 12 bar
mediu de operare	Aer comprimat conform ISO 8573-1:2010 [7::-]
Conformitatea PWIS	VDMA24364-zona III
Tip de protectie	IP54
Temperatura mediului	-50 ... 60 °C
Greutate produs	14 g
tip fixare	insurubabil cu filet exterior
Indicatie material	conform RoHS
Materialul surubului de ventilare	HP PA 12