


Operatör paneli FED-710

Ürün numarası: 543443

FESTO

Display and operator unit with LCD graphic display for connecting to PLC systems.

Products to be discontinued. Available until 2010.



Bilgi sayfası

Özellik	Değer
Depth	71 mm
Yükseklik	187 mm
Uzunluk	232 mm
Max. front panel thickness	5 mm
User memory	32 Mbyte
Real-time clock	evet
Real-time clock deviation	130 s / month
Number of colours	64 k
Gösterge	TFT colour
Display property	Touchscreen
Display size	7,5"
Backup battery	3 V / 270 mA lityum
Operating voltage range DC	18 ... 30 V
Display resolution	VGA, 640x480 Pixel
Nominal çalışma gerilimi DC	24 V
Nominal çalışma gerilimindeki akım tüketimi	1,1 A
CE mark (see declaration of conformity)	to EU directive for EMC
Depolama sıcaklığı	-20 ... 70 °C
Relatif hava nemi	5 - 85 % yoğunlaşmayan
Koruma sınıfı	IP65 front, IP20 back
Çevre sıcaklığı	0 ... 45 °C
Müsaade edilebilirlik	C-Tick c UL us - Listed (OL)
Ürün ağırlığı	1.600 g
AUX interface	Sub-D 9-pinli Soket
Printer interface	RS232 Sub-D 15-pin Soket
PLC interface	RS232 Sub-D 15-pin Erkek soket
USB interface	evet
Ethernet arabirimi	RJ45 10/100 MBd 2nd Ethernet interface, optical 10 MBd
Bağlantı şekli	Ön panel montajı
Malzeme hakkında not	Conforms to RoHS