

堵頭

QSC-10H-50

料號: 130702

FESTO



技術參數

| 特性 | 值 |
|--|---|
| 尺寸 | 標準 |
| 裝配位置 | 任何 |
| 設計 | Blanking plug |
| 容器尺寸 | 50 |
| Operating pressure for entire temperature range 操作壓力的完整溫度範圍 | -0.095 ... 0.6 MPa -0.95 ... 6 bar |
| Operating pressure for entire temperature range | -13.775 ... 87 psi |
| Temperature-dependent operating pressure 溫度取決於操作壓力 | -0.095 ... 1.4 MPa -0.95 ... 14 bar |
| Temperature-dependent operating pressure | -13.775 ... 203 psi |
| Maritime classification 操作介質 | see certificate 壓縮空氣符合 ISO8573-1:2010 [7:-:-] Water as per manufacturer's declaration at www.festo.com |
| 注意: 操作和嚮導介質 | 潤滑操作可行 |
| 耐腐蝕等級 CRC | 1 - Low corrosion stress |
| PWIS conformity | VDMA24364-B1/B2-L |
| 環境溫度 | -10 ... 80 °C |
| 產品重量 | 2 g |
| 氣壓連接, 氣口 1 | Push-in sleeve diameter 10 mm |
| 材料備註 | 符合 RoHS |
| Material housing | PBT |