


# L型快插接頭

## QSL-6-100

料號: 130741

FESTO



### 技術參數

特性	值
尺寸	標準
額定尺寸	5 mm
裝配位置	任何
設計	L-shape
容器尺寸	100
設計結構	推/拉原理
Operating pressure for entire temperature range	-0.095 ... 0.6 MPa
操作壓力的完整溫度範圍	-0.95 ... 6 bar
Operating pressure for entire temperature range	-13.775 ... 87 psi
Temperature-dependent operating pressure	-0.095 ... 1.4 MPa
溫度取決於操作壓力	-0.95 ... 14 bar
Temperature-dependent operating pressure	-13.775 ... 203 psi
Maritime classification	see certificate
操作介質	壓縮空氣符合 ISO8573-1:2010 [7:-:-] Water as per manufacturer's declaration at <a href="http://www.festo.com">www.festo.com</a>
注意: 操作和嚮導介質	潤滑操作可行
耐腐蝕等級 CRC	1 - Low corrosion stress
PWIS conformity	VDMA24364-B1/B2-L
環境溫度	-10 ... 80 °C
產品重量	7.3 g
氣壓連接, 氣口 1	For tubing outside diameter 6 mm
氣壓連接, 氣口 2	For tubing outside diameter 6 mm
釋放環的顏色	藍色
材料備註	符合 RoHS
Material housing	PBT
Material release ring	POM
Material of tubing seal	NBR
Material of tube retaining claw	高合金鋼, 耐腐蝕