

# L型快插式螺紋接頭

## QSM1-1/8-6-100

料號: 130765

FESTO

360° orientable, male thread with external hexagon.



### 技術參數

| 特性  | 值                                |
|---|----------------------------------|
| 尺寸  | Mini型                            |
| 額定尺寸  | 3.3 mm                           |
| 柱頭螺栓上的密封件類型                                     | 外表層                              |
| 裝配位置  | 任何                               |
| 設計  | L-shape                          |
| 容器尺寸  | 100                              |
| 設計結構  | 推/拉原理                            |
| Operating pressure for entire temperature range | -0.095 ... 0.6 MPa               |
| 操作壓力的完整溫度範圍                                     | -0.95 ... 6 bar                  |
| Operating pressure for entire temperature range | -13.775 ... 87 psi               |
| Temperature-dependent operating pressure        | -0.095 ... 1.4 MPa               |
| 溫度取決於操作壓力                                       | -0.95 ... 14 bar                 |
| Temperature-dependent operating pressure        | -13.775 ... 203 psi              |
| Maritime classification                         | see certificate                  |
| 操作介質  | 壓縮空氣符合 ISO8573-1:2010 [7:-:-]    |
| 注意: 操作和嚮導介質                                     | 潤滑操作可行                           |
| 耐腐蝕等級 CRC                                       | 1 - Low corrosion stress         |
| PWIS conformity                                 | VDMA24364-B1/B2-L                |
| 環境溫度  | -10 ... 80 °C                    |
| 額定鎖緊扭矩  | 7 Nm                             |
| 額定擰緊扭矩公差  | ± 20 %                           |
| 產品重量  | 7 g                              |
| 安裝類型  | External hex A/F 10              |
| 氣壓連接, 氣口 1                                      | 外螺紋 R1/8                         |
| 氣壓連接, 氣口 2                                      | For tubing outside diameter 6 mm |
| 釋放環的顏色  | 藍色                               |
| 材料備註  | 符合 RoHS                          |
| Material housing                                | PBT                              |
| Material release ring                           | POM                              |
| Material of tubing seal                         | NBR                              |
| Material of tube retaining claw                 | 高合金鋼, 耐腐蝕                        |