

# 馬達電纜


## NEBM-S1G9-E-7-Q5-LE6

料號: 1450371

★ Kernprogramm

適用於伺服馬達EMMS-ST...

FESTO



### 技術參數

| 特性   | 值                                    |
|--|--------------------------------------|
| Cable identification                                 | Without inscription label holder     |
| Electrical connection 1, function                    | Field device side                    |
| Electrical connection 1, design                      | 有角的                                  |
| Electrical connection 1, connection type             | 插頭插座                                 |
| Electrical connection 1, cable outlet                | 直的                                   |
| Electrical connection 1, connection technology       | Sub-D                                |
| Electrical connection 1, number of pins/wires        | 9                                    |
| Electrical connection 1, occupied pins/wires         | 6                                    |
| Electrical connection 2, function                    | Controller side                      |
| Electrical connection 2, connection type             | 電纜                                   |
| Electrical connection 2, connection technology       | 開放式終端                                |
| Electrical connection 2, number of pins/wires        | 6                                    |
| Electrical connection 2, occupied pins/wires         | 6                                    |
| 工作電壓範圍 DC  | 0 ... 72 V                           |
| 額定工作電壓 DC  | 24 V                                 |
| 電纜長度   | 7 m                                  |
| 電纜屬性   | Suitable for energy chains           |
| Bending radius, flexible cable installation          | >= 62 mm                             |
| 電纜直徑   | 6.2 mm                               |
| 電纜結構   | 6x0,34<br>已屏蔽                        |
| 導體的額定截面  | 0.34 mm <sup>2</sup>                 |
| 導線末端   | 導線末端套圈                               |
| 防護等級   | IP65                                 |
| Note on degree of protection                         | 裝配狀態                                 |
| 環境溫度   | -40 ... 80 °C                        |
| Ambient temperature with flexible cable installation | -5 ... 80 °C                         |
| CE 符號 (參見符合的標準)                                      | in accordance with EU RoHS directive |
| UKCA marking (see declaration of conformity)         | To UK RoHS instructions              |
| PWIS conformity                                      | VDMA24364-B2-L                       |
| 材料備註   | 符合 RoHS                              |
| 耐腐蝕等級 CRC  | 0 - No corrosion stress              |
| Material cable sheath                                | TPE-U(PUR)                           |
| 電纜外套顏色   | 灰色                                   |