


T形快插接頭

QSTF-1/8-4-B

料號: 153182

FESTO

360° orientable, male and female thread with external hexagon.



技術參數

特性	值
尺寸	標準
額定尺寸	2.8 mm
柱頭螺栓上的密封件類型	外表層
裝配位置	任何
設計	L-shape, additional connection, female thread, lengthwise
容器尺寸	1
設計結構	推/拉原理
Operating pressure for entire temperature range	-0.095 ... 0.6 MPa
操作壓力的完整溫度範圍	-0.95 ... 6 bar
Operating pressure for entire temperature range	-13.775 ... 87 psi
Temperature-dependent operating pressure	-0.095 ... 1.4 MPa
溫度取決於操作壓力	-0.95 ... 14 bar
Temperature-dependent operating pressure	-13.775 ... 203 psi
Maritime classification	see certificate
操作介質	壓縮空氣符合 ISO8573-1:2010 [7:-:-] Water as per manufacturer's declaration at www.festo.com
注意: 操作和嚮導介質	潤滑操作可行
耐腐蝕等級 CRC	1 - Low corrosion stress
PWIS conformity	VDMA24364-B1/B2-L
環境溫度	-10 ... 80 °C
額定鎖緊扭矩	7 Nm
額定擰緊扭矩公差	± 20 %
產品重量	22 g
輸出數量	2
輸送管線的數量	1
安裝類型	External hex A/F 14
氣壓連接, 氣口 1	外螺紋 R1/8
氣壓連接, 氣口 2	內螺紋 G1/8 For tubing outside diameter 4 mm
釋放環的顏色	藍色
材料備註	符合 RoHS
Material housing	PBT
Material hollow bolt	Nickel-plated brass
Material release ring	POM
Material of tubing seal	NBR
Material of tube retaining claw	高合金鋼, 耐腐蝕