


L型快插式螺紋接頭

QSL-V0-3/8-8

料號: 160517

FESTO

360° orientable, male thread with external hexagon.



技術參數

特性	值
尺寸	標準
額定尺寸	6.7 mm
Material fire test	UL94 V-0 (housing) UL94 V-0 (releasing ring)
柱頭螺柱上的密封件類型	外表層
設計	L-shape
容器尺寸	10
設計結構	推/拉原理
Operating pressure for entire temperature range	-0.095 ... 1 MPa
操作壓力的完整溫度範圍	-0.95 ... 10 bar
Operating pressure for entire temperature range	-13.775 ... 145 psi
操作壓力注意事項	Water: max. 0.6 MPa at max. 50°C
操作介質	壓縮空氣符合 ISO8573-1:2010 [7:-:-] Water (liquid, free of ice)
注意: 操作和嚮導介質	潤滑操作可行
耐腐蝕等級 CRC	2 - Moderate corrosion stress
PWIS conformity	VDMA24364-B1/B2-L
環境溫度	0 ... 60 °C
額定鎖緊扭矩	15.5 Nm
額定擰緊扭矩公差	± 20 %
產品重量	32 g
安裝類型	External hex A/F 17
氣壓連接, 氣口 1	外螺紋 R3/8
氣壓連接, 氣口 2	For tubing outside diameter 8 mm
釋放環的顏色	黑色
Material of threaded plug	鍍鎳黃銅
材料備註	符合 RoHS
Material housing	PBT
Material release ring	PBT
Material of tubing seal	NBR
Material of tube retaining claw	高合金鋼, 耐腐蝕 黃銅