


# 插入連接件

## QS-V0-12

料號: 160549

FESTO



### 技術參數

特性	值
尺寸	標準
額定尺寸	11 mm
Material fire test	UL94 V-0 (housing) UL94 V-0 (releasing ring)
設計	直式結構
容器尺寸	1
設計結構	推/拉原理
Operating pressure for entire temperature range	-0.095 ... 1 MPa
操作壓力的完整溫度範圍	-0.95 ... 10 bar
Operating pressure for entire temperature range	-13.775 ... 145 psi
操作壓力注意事項	Water: max. 0.6 MPa at max. 50°C
操作介質	壓縮空氣符合 ISO8573-1:2010 [7:-:-] Water (liquid, free of ice)
注意: 操作和嚮導介質	潤滑操作可行
耐腐蝕等級 CRC	2 - Moderate corrosion stress
PWIS conformity	VDMA24364-B1/B2-L
環境溫度	0 ... 60 °C
產品重量	25 g
氣壓連接, 氣口 1	For tubing outside diameter 12 mm
氣壓連接, 氣口 2	For tubing outside diameter 12 mm
釋放環的顏色	黑色
材料備註	符合 RoHS
Material housing	PBT
Material release ring	PBT
Material of tubing seal	NBR
Material of tube retaining claw	高合金鋼, 耐腐蝕 黃銅