

塑料氣管 PUN-4X0,75-RT

料號: 178410

FESTO

具有標準外徑的氣管，用於QS快插接頭，CN和CK 聚氨酯 接頭
(不可用於食品行業)。



技術參數

| 特性 | 值 |
|---|--|
| 外徑 | 4 mm |
| 與流量相關的彎曲半徑 | 17 mm |
| 內徑 | 2.6 mm |
| 最小彎曲半徑 | 8 mm |
| Instructions for use | TPE-U Ester based The plastic tubing can only be installed in contact with cables if the sheathing is free from phosphoric acid esters. Otherwise the plastic tubing can get damaged. |
| Tubing characteristics | Suitable for energy chains |
| Operating pressure for entire temperature range | -0.095 ... 0.7 MPa |
| 操作壓力的完整溫度範圍 | -0.95 ... 7 bar |
| Operating pressure for entire temperature range | -13.775 ... 101.5 psi |
| Temperature-dependent operating pressure | -0.095 ... 1 MPa |
| 溫度取決於操作壓力 | -0.95 ... 10 bar |
| Temperature-dependent operating pressure | -13.775 ... 145 psi |
| 授權 | TÜV |
| 認證核發部門 | B 013277 0506 00 |
| 操作介質 | 壓縮空氣符合 ISO8573-1:2010 [7:-:-] |
| Material fire test | UL94 HB |
| PWIS conformity | VDMA24364-B2-L |
| 環境溫度 | -35 ... 60 °C |
| 產品重量視長度而定 | 0.0089 kg/m |
| 氣壓連接 | For push-in connector outside diameter 4 mm 用於倒鉤接頭內徑 3 mm 具螺母 用於倒鉤接頭內徑 3 mm |
| 顏色 | 紅色 |
| 肖氏硬度 | D 52 +/-3 |
| 材料備註 | 符合 RoHS |
| Material tubing | TPE-U(PU) |