

# 塑料氣管 PUN-H-3X0,5-SW

料號: 197389

FESTO

可用於食品加工行業(耐水解).  
產品不適合用於CN和PK快插管接頭



## 技術參數

| 特性  | 值  |
|---|--|
| 外徑  | 3 mm   |
| 與流量相關的彎曲半徑                                      | 12 mm  |
| 內徑  | 2.1 mm   |
| 最小彎曲半徑  | 6 mm   |
| Instructions for use                            | TPE-U Ether basiert  |
| Tubing characteristics                          | Suitable for energy chains   |
| Operating pressure for entire temperature range | -0.095 ... 0.6 MPa   |
| 操作壓力的完整溫度範圍                                     | -0.95 ... 6 bar  |
| Operating pressure for entire temperature range | -13.775 ... 87 psi   |
| Temperature-dependent operating pressure        | -0.095 ... 1 MPa   |
| 溫度取決於操作壓力                                       | -0.95 ... 10 bar   |
| Temperature-dependent operating pressure        | -13.775 ... 145 psi  |
| 操作壓力注意事項  | Water: temperature-dependent operating pressure, see diagram, max. 0.3 MPa at 0 - 60°C   |
| 授權  | TÜV  |
| 認證核發部門  | B 013277 0506 00   |
| 操作介質  | 壓縮空氣符合 ISO8573-1:2010 [7:-:-]<br>Water (liquid, free of ice)   |
| Material fire test                              | UL94 HB  |
| PWIS conformity                                 | VDMA24364-B2-L   |
| RSBP classification to CD-0033                  | F1a  |
| 無塵室等級   | This product is a static object, active particle generation is not possible when used correctly.<br>Clean product before using it in a cleanroom environment and ensure it is installed correctly. |
| Food-safe                                       | See Supplementary material information   |
| 環境溫度  | -35 ... 60 °C  |
| 產品重量視長度而定                                       | 0.0042 kg/m  |
| 氣壓連接  | For push-in connector outside diameter 3 mm  |
| 顏色  | 黑色   |
| 肖氏硬度  | D 52 +/-3  |
| 材料備註  | 符合 RoHS  |
| Material tubing                                 | TPE-U(PU)  |