


連接電纜

NEBM-H7G2-E-10-Q14N-LE2

料號: 5219208

★ Kernprogramm

FESTO



技術參數

特性	值
Cable identification	Without inscription label holder
Electrical connection 1, function	Field device side
Electrical connection 1, design	有角的
Electrical connection 1, connection type	插頭插座
Electrical connection 1, cable outlet	直的
Electrical connection 1, connection technology	Connection pattern H7, coded for the motor brake
Electrical connection 1, number of pins/wires	2
Electrical connection 1, occupied pins/wires	2
Electrical connection 2, function	Controller side
Electrical connection 2, connection type	電纜
Electrical connection 2, connection technology	開放式終端
Electrical connection 2, number of pins/wires	2
Electrical connection 2, occupied pins/wires	2
工作電壓範圍 DC	0 ... 30 V
工作電壓範圍 AC	0 ... 30 V
在40°C時的可接受電流負載	5 A
浪湧強度	2 kV
電纜長度	10 m
電纜屬性	Suitable for energy chains
電纜的測試條件	視需求的測試條件
Bending radius, fixed cable installation	>= 27 mm
Bending radius, flexible cable installation	>= 55 mm
電纜直徑	5.1 mm
電纜結構	2x0,51
導體的額定截面	0.51 mm ²
Nominal conductor cross section (AWG)	AWG20
導線末端	導線末端套圈
防護等級	IP20
Note on degree of protection	裝配狀態
環境溫度	-40 ... 80 °C
Ambient temperature with flexible cable installation	-10 ... 80 °C
CE 符號 (參見符合的標準)	in accordance with EU RoHS directive
UKCA marking (see declaration of conformity)	To UK RoHS instructions
PWIS conformity	VDMA24364 zone III
材料備註	符合 RoHS
污染程度	3
耐腐蝕等級 CRC	0 - No corrosion stress
Material cable sheath	PVC
電纜外套顏色	黑色
Material housing	PA
外殼顏色	白色
Material insulation	PVC