

連接電纜

KMP6-15P-12-2,5



料號: 527543

Classic - nicht für Neukonstruktionen verwenden

用於閩島 CPV-SC, 具 15-pin Sub-D 插頭, 2.5 m 長.

Modern alternatives can be found by entering the first four characters of the type code in the search field.

FESTO



技術參數

特性	值
符合標準	DIN 41652
Cable identification	Without inscription label holder
連接頻率	50
產品重量	293 g
Electrical connection 1, function	Field device side
Electrical connection 1, design	有角的
Electrical connection 1, connection type	插頭插座
Electrical connection 1, cable outlet	直的
Electrical connection 1, connection technology	Sub-D
Electrical connection 1, number of pins/wires	15
Electrical connection 1, occupied pins/wires	15
Electrical connection 1, type of mounting	2 screws 4-40 UNC
Electrical connection 2, function	Controller side
Electrical connection 2, connection type	電纜
Electrical connection 2, connection technology	開放式終端
Electrical connection 2, number of pins/wires	15
Electrical connection 2, occupied pins/wires	15
工作電壓範圍 DC	0 ... 30 V
額定工作電壓 DC	24 V
在40°C時的可接受電流負載	2.8 A
浪湧強度	1 kV
電纜長度	2.5 m
電纜屬性	標準
電纜的測試條件	視需求的測試條件
Bending radius, fixed cable installation	>= 86 mm
Bending radius, flexible cable installation	>= 129 mm
電纜直徑	8.6 mm
電纜直徑公差	± 0,25 mm
電纜結構	15x0,34
導體的額定截面	0.34 mm ²
導線末端	Cut off bluntly
防護等級	IP40
Note on degree of protection	裝配狀態
環境溫度	-25 ... 70 °C
Ambient temperature with flexible cable installation	-5 ... 70 °C
儲藏溫度	-20 ... 75 °C
CE 符號 (參見符合的標準)	in accordance with EU RoHS directive
UKCA marking (see declaration of conformity)	To UK RoHS instructions
PWIS conformity	VDMA24364-B2-L
材料備註	符合 RoHS
污染程度	2
Material cable sheath	PVC

特性	值
電纜外套顏色	灰色
Material housing	PBT-加強
外殼顏色	灰色
Material screw-type lock	Nickel-plated brass
Material electrical contact	Gold-plated copper alloy