

聯合螺栓 MCK-PK-3-KD

料號: 533672

FESTO

金屬結構.



技術參數

| 特性 | 值 |
|---|---|
| 尺寸 | 內螺紋 M6x0.75 |
| Operating pressure for entire temperature range | -0.095 ... 1.2 MPa |
| 操作壓力的完整溫度範圍 | -0.95 ... 12 bar |
| Operating pressure for entire temperature range | -13.775 ... 174 psi |
| 耐腐蝕等級 CRC | 1 - Low corrosion stress |
| PWIS conformity | VDMA24364-B2-L |
| 環境溫度 | -10 ... 60 °C |
| 氣壓連接, 氣口 1 | For tubing outside diameter 4 mm 用於倒鉤接頭內徑 3 mm 具螺母 |
| Material of union nut | Wrought aluminium alloy, nickel-plated |
| 材料備註 | 符合 RoHS |