

密封圈

OL-1/4-200

料號: 534233

FESTO

防洩漏, 具金屬殼體



技術參數

| 特性 | 值 |
|--|--|
| 基於標準 | ISO 16030 |
| 容器尺寸 | 200 |
| Operating pressure for entire temperature range 操作壓力的完整溫度範圍 | -0.095 ... 3 MPa -0.95 ... 30 bar |
| Operating pressure for entire temperature range | -13.775 ... 435 psi |
| 耐腐蝕等級 CRC | 2 - Moderate corrosion stress |
| PWIS conformity | VDMA24364-B2-L |
| RSBP classification to CD-0033 | F1a |
| 無塵室等級 | This product is a static object, active particle generation is not possible when used correctly. Clean product before using it in a cleanroom environment and ensure it is installed correctly. |
| 環境溫度 | -40 ... 100 °C |
| 環境溫度下手動緊固 | 是 |
| 額定鎖緊扭矩 | 10 Nm |
| 額定擰緊扭矩公差 | ± 20 % |
| 氣壓連接 | G1/4 |
| 材料備註 | 符合 RoHS |
| Material stops | 鋁 |
| Material seals | HNBR |