

# 塑料氣管

## PLN-12X1,75-RT

料號: 558221

FESTO

具高度耐化學腐蝕和耐水解能力



### 技術參數

特性	值
外徑	12 mm
與流量相關的彎曲半徑	65 mm
內徑	8.4 mm
最小彎曲半徑	23 mm
Temperature-dependent operating pressure	-0.095 ... 1.4 MPa
溫度取決於操作壓力	-0.95 ... 14 bar
Temperature-dependent operating pressure	-13.775 ... 203 psi
操作壓力注意事項	Water: max. 0.6 MPa at 0 - 50 °C
授權	TÜV
認證核發部門	B 013277 0506 00
操作介質	壓縮空氣符合 ISO8573-1:2010 [7:-:-] Water (liquid, free of ice)
PWIS conformity	VDMA24364-B2-L
無塵室等級	This product is a static object, active particle generation is not possible when used correctly. Clean product before using it in a cleanroom environment and ensure it is installed correctly.
Food-safe	See Supplementary material information
環境溫度	-30 ... 80 °C
產品重量視長度而定	0.054 kg/m
氣壓連接	For push-in connector outside diameter 12 mm
顏色	紅色
材料備註	符合 RoHS
Material tubing	PE