

# 塑料氣管

## PUN-H-1/2-BR-150-CB

料號: 567999

FESTO

可用於食品加工行業 (耐水解).



### 技術參數

特性	值
外徑, 英寸	1/2
與流量相關的彎曲半徑	0.204 ft
最小彎曲半徑	0.075 ft
Tubing characteristics	Suitable for energy chains in applications with high cycle rates
Tubing test conditions	Suitable for energy chains: > 5 million cycles to FN 942021
溫度取決於操作壓力	-14.4 ... 145 Psi
操作介質	壓縮空氣符合 ISO8573-1:2010 [7:-:-] Water as per manufacturer's declaration at <a href="http://www.festo.com">www.festo.com</a>
Food-safe	See Supplementary material information
環境溫度	-31 ... 145 °F
產品重量視長度而定	0.88 oz/ft
氣壓連接	For push-in connector outside diameter 1/2"
顏色	棕色
肖氏硬度	D 52 +/-3
材料備註	不含黃銅和聚四氟乙烯 符合 RoHS
Material tubing	TPE-U(PU)