

# 塑料氣管 PAN-14X2-SI

料號: 570392

FESTO



## 技術參數

特性	值
外徑	14 mm
與流量相關的彎曲半徑	80 mm
內徑	10 mm
最小彎曲半徑	50 mm
Tubing characteristics	Suitable for energy chains
Temperature-dependent operating pressure	-0.095 ... 1.7 MPa
溫度取決於操作壓力	-0.95 ... 17 bar
Temperature-dependent operating pressure	-13.775 ... 246.5 psi
授權	TÜV
Maritime classification	see certificate
認證核發部門	B 013277 0506 00
操作介質	壓縮空氣符合 ISO8573-1:2010 [7:-:-]
PWIS conformity	VDMA24364-B2-L
環境溫度	-30 ... 80 °C
產品重量視長度而定	0.077 kg/m
氣壓連接	For push-in connector outside diameter 14 mm
顏色	銀
肖氏硬度	D 55 +/-3
材料備註	符合 RoHS
Material tubing	TPE-A