



## 連接電纜

### NEBS-L1G4-K-2.5-LE4

料號: 572576

★ Kernprogramm

FESTO



## 技術參數

特性	值
Cable identification	With inscription label holder
連接頻率	100
產品重量	53 g
Electrical connection 1, function	Field device side
Electrical connection 1, design	有角的
Electrical connection 1, connection type	插頭插座
Electrical connection 1, cable outlet	直的
Electrical connection 1, connection technology	Connection pattern L1J
Electrical connection 1, number of pins/wires	4
Electrical connection 1, occupied pins/wires	4
Electrical connection 1, type of mounting	Snap-in locking
Electrical connection 2, function	Controller side
Electrical connection 2, connection type	電纜
Electrical connection 2, connection technology	開放式終端
Electrical connection 2, number of pins/wires	4
Electrical connection 2, occupied pins/wires	4
工作電壓範圍 DC	0 ... 30 V
在40°C時的可接受電流負載	1 A
浪湧強度	0.8 kV
電纜長度	2.5 m
電纜屬性	標準
電纜的測試條件	視需求的測試條件
Bending radius, fixed cable installation	$\geq 13$ mm
Bending radius, flexible cable installation	$\geq 42$ mm
電纜直徑	4.1 mm
電纜直徑公差	$\pm 0,2$ mm
電纜結構	4x0,17
導體的額定截面	0.17 mm <sup>2</sup>
導線末端	Cut off bluntly
防護等級	IP40
Note on degree of protection	裝配狀態
環境溫度	-20 ... 60 °C
Ambient temperature with flexible cable installation	-5 ... 60 °C
儲藏溫度	-20 ... 60 °C
CE 符號 (參見符合的標準)	in accordance with EU RoHS directive
UKCA marking (see declaration of conformity)	To UK RoHS instructions
PWIS conformity	VDMA24364 zone III
材料備註	符合 RoHS
污染程度	2
耐腐蝕等級 CRC	4 - Very high corrosion stress
Material cable sheath	PVC
電纜外套顏色	灰色
Material housing	PA
外殼顏色	白色
Material electrical contact	Tin-plated bronze
Material insulation	PVC