

# 插入式穿板接頭 NPQH-H-Q8-E-P10

料號: 578301

FESTO



## 技術參數

特性	值
尺寸	標準
額定尺寸	7 mm
Tubing insertion depth	16 mm
裝配位置	任何
設計	Bulkhead
容器尺寸	10
設計結構	推/拉原理
Operating pressure for entire temperature range	-0.095 ... 2 MPa
操作壓力的完整溫度範圍	-0.95 ... 20 bar
Operating pressure for entire temperature range	-13.775 ... 290 psi
操作壓力注意事項	Water: max. 0.6 MPa at 0 - 50 °C
認證核發部門	NSF C0523185
操作介質	壓縮空氣符合 ISO8573-1:2010 [7:-:-] Water (liquid, free of ice)
注意: 操作和嚮導介質	潤滑操作可行
耐腐蝕等級 CRC	3 - High corrosion stress
PWIS conformity	VDMA24364-B1/B2-L
無塵室等級	ISO class 4
Food-safe	See declaration of conformity NSF/ANSI 169
環境溫度	0 ... 150 °C
產品重量	40.6 g
安裝類型	External hexagon A/F 20
氣壓連接, 氣口 1	For tubing outside diameter 8 mm
氣壓連接, 氣口 2	For tubing outside diameter 8 mm
材料備註	符合 RoHS
Material housing	Brass, chemically nickel-plated
Guard ring material	PEI
Material release ring	Brass, chemically nickel-plated
Material nut	Brass, chemically nickel-plated
Material of tubing seal	FPM
Material of tube retaining claw	高合金鋼, 耐腐蝕
Thrust ring material	PEI