

插入接頭

NPQH-D-G14-Q12-P10

料號: 578344

FESTO



技術參數

| 特性 | 值 |
|---|--|
| 尺寸 | 標準 |
| 額定尺寸 | 8 mm |
| Tubing insertion depth | 19.5 mm |
| 柱頭螺栓上的密封件類型 | 密封圈 |
| 裝配位置 | 任何 |
| 設計 | 直式結構 |
| 容器尺寸 | 10 |
| 設計結構 | 推/拉原理 |
| Operating pressure for entire temperature range | -0.095 ... 2 MPa |
| 操作壓力的完整溫度範圍 | -0.95 ... 20 bar |
| Operating pressure for entire temperature range | -13.775 ... 290 psi |
| 操作壓力注意事項 | Water: max. 0.6 MPa at 0 - 50 °C |
| 認證核發部門 | NSF C0523185 |
| 操作介質 | 壓縮空氣符合 ISO8573-1:2010 [7:-:-] Water (liquid, free of ice) |
| 注意: 操作和嚮導介質 | 潤滑操作可行 |
| 耐腐蝕等級 CRC | 3 - High corrosion stress |
| PWIS conformity | VDMA24364-B1/B2-L |
| 無塵室等級 | ISO class 4 |
| Food-safe | See declaration of conformity NSF/ANSI 169 |
| 環境溫度 | 0 ... 150 °C |
| 額定鎖緊扭矩 | 7.5 Nm |
| 額定擰緊扭矩公差 | ± 20 % |
| 產品重量 | 26.6 g |
| 安裝類型 | External hexagon A/F 19 Internal hex A/F 8 |
| 氣壓連接, 氣口 1 | 外螺紋 G1/4 |
| 氣壓連接, 氣口 2 | For tubing outside diameter 12 mm |
| 材料備註 | 符合 RoHS |
| Material housing | Brass, chemically nickel-plated |
| Material of threaded seal | FPM |
| Guard ring material | PEI |
| Material release ring | Brass, chemically nickel-plated |
| Material of tubing seal | FPM |
| Material of tube retaining claw | 高合金鋼, 耐腐蝕 |
| Thrust ring material | PEI |