

ring light SBAL-C6-R-R-D

料號: 8031162
將停止供貨的產品

FESTO

Type to be discontinued. Available until 2024. See Support Portal for alternative products.



技術參數

| 特性 | 值 |
|---|--|
| CE 符號 (參見符合的標準) | 根據 EU-EMV 指導原則 in accordance with EU RoHS directive |
| UKCA marking (see declaration of conformity) | To UK instructions for EMC To UK RoHS instructions |
| 授權 | RCM Mark |
| 工作距離 | 100 - 300 mm |
| Lighting type | Ring light |
| 光的類型 | 紅色 LED Diffuse |
| Wavelength | 630 nm |
| 電氣連接 | 12-pin 2x M12 插頭 |
| Trigger level | Level 18 V ... UB |
| 額定工作電壓 DC | 24 V |
| 容許的電壓波動 | +/- 5 % |
| 殘餘波動 | 5 % |
| Current consumption during continuous operation | 290 mA |
| Current consumption during flash operation | 290 mA |
| Maximum number of devices connectable in series | 2 |
| 極性保護 | 用於所有電接口 |
| Ambient temperature during continuous operation | 0 ... 35 °C |
| Ambient temperature during flash operation | 0 ... 50 °C |
| 儲藏溫度 | -20 ... 60 °C |
| 防護等級 | IP67 |
| PWIS conformity | VDMA24364-B2-L |
| 產品重量 | 150 g |
| 安裝類型 | 具安裝支架 |
| Material housing | 鋁 電鍍 |
| 材料備註 | 符合 RoHS |