

塑料氣管

PTFEN-16X2,5-NT-25

料號: 8061177

FESTO



技術參數

| 特性 | 值 |
|---|--|
| 外徑 | 16 mm |
| 與流量相關的彎曲半徑 | 160 mm |
| 內徑 | 11 mm |
| 最小彎曲半徑 | 109 mm |
| Instructions for use | Tubing without printing |
| Operating pressure for entire temperature range | -0.095 ... 0.5 MPa |
| 操作壓力的完整溫度範圍 | -0.95 ... 5 bar |
| Operating pressure for entire temperature range | -13.775 ... 72.5 psi |
| Temperature-dependent operating pressure | -0.095 ... 1.2 MPa |
| 溫度取決於操作壓力 | -0.95 ... 12 bar |
| Temperature-dependent operating pressure | -13.775 ... 174 psi |
| 操作介質 | 壓縮空氣符合 ISO8573-1:2010 [7:-:-] |
| Material fire test | UL94 V-0 |
| PWIS conformity | VDMA24364-B1/B2-L |
| 無塵室等級 | This product is a static object, active particle generation is not possible when used correctly. Clean product before using it in a cleanroom environment and ensure it is installed correctly. |
| Food-safe | See Supplementary material information |
| 環境溫度 | -20 ... 150 °C |
| 產品重量視長度而定 | 0.228 kg/m |
| 氣壓連接 | For push-in connector outside diameter 16 mm |
| 顏色 | 中性 |
| 肖氏硬度 | D 55 +/-5 |
| 材料備註 | 符合 RoHS |
| Material tubing | PTFE |