



連接電纜

NEBC-M12G5-S-1,5-N-M12G5

料號: 8085741

FESTO



技術參數

特性	值
Cable identification	具配件
連接頻率	500
產品重量	163 g
Electrical connection 1, function	Field device side
Electrical connection 1, design	圓形
Electrical connection 1, connection type	插頭
Electrical connection 1, cable outlet	直的
Electrical connection 1, connection technology	M12x1, A-coded in accordance with EN 61076-2-101
Electrical connection 1, number of pins/wires	5
Electrical connection 1, occupied pins/wires	5
Electrical connection 1, type of mounting	Screw lock
Electrical connection 2, function	Controller side
Electrical connection 2, design	圓形
Electrical connection 2, connection type	插頭
Electrical connection 2, cable outlet	直的
Electrical connection 2, connection technology	M12x1, A-coded in accordance with EN 61076-2-101
Electrical connection 2, number of pins/wires	5
Electrical connection 2, occupied pins/wires	5
Electrical connection 2, type of mounting	Screw lock
工作電壓範圍 DC	0 ... 30 V
工作電壓範圍 AC	0 ... 30 V
在40°C時的可接受電流負載	4 A
浪湧強度	0.8 kV
電纜長度	1.5 m
電纜屬性	標準
電纜的測試條件	視需求的測試條件
電纜直徑	5 mm
電纜結構	4x0,34 已屏蔽
導體的額定截面	0.34 mm ²
防護等級	IP65 IP67
Note on degree of protection	裝配狀態
環境溫度	-25 ... 70 °C
Ambient temperature with flexible cable installation	-5 ... 70 °C
CE 符號 (參見符合的標準)	in accordance with EU RoHS directive
UKCA marking (see declaration of conformity)	To UK RoHS instructions
PWIS conformity	VDMA24364-B2-L
材料備註	符合 RoHS
污染程度	3
耐腐蝕等級 CRC	2 - Moderate corrosion stress
Material cable sheath	TPE-U(PUR)
電纜外套顏色	淡灰色
Material housing	TPE-U(PUR)
外殼顏色	黑色
Material screw-type lock	Nickel-plated brass
Material electrical contact	Gold-plated bronze Brass, gold-plated
Material insulation	PVC