


馬達電纜

NEBM-M40G8-E-5-Q10N-LE8-1

料號: 8085961
將停止供貨的產品

For EMMS-AS-190 with CMMT-AS.

FESTO



技術參數

特性	值
Cable identification	Without inscription label holder
產品重量	1,800 g
Electrical connection 1, function	Field device side
Electrical connection 1, design	圓形
Electrical connection 1, connection type	插頭插座
Electrical connection 1, cable outlet	直的
Electrical connection 1, connection technology	M40x1,5
Electrical connection 1, number of pins/wires	8
Electrical connection 1, occupied pins/wires	8
Electrical connection 2, function	Controller side
Electrical connection 2, connection type	電纜
Electrical connection 2, connection technology	開放式終端
Electrical connection 2, number of pins/wires	8
Electrical connection 2, occupied pins/wires	8
工作電壓範圍 DC	0 ... 630 V
Note on operating voltage range DC	0 - 300 V for 0.75 mm ²
工作電壓範圍 AC	0 ... 630 V
Note on operating voltage range AC	0 - 300 V for 0.75 mm ²
在40°C時的可接受電流負載	22 A
Note on acceptable current load at 40°C	12 A for 0.75 mm ²
浪湧強度	4 kV
Note on surge resistance	2.5 kV for 0.75 mm ²
電纜長度	5 m
電纜屬性	適合於拖鏈
Bending radius, fixed cable installation	>= 70 mm
Bending radius, flexible cable installation	>= 140 mm
電纜直徑	14 mm
電纜結構	4x2,5+2x(2x0,75) 已屏蔽
導體的額定截面	0.75 mm ² 2.5 mm ²
導線末端	Cable end sleeve to DIN 46228-A...-10 Cable end sleeve to DIN 46228-E...-10
防護等級	IP65
Note on degree of protection	裝配狀態
環境溫度	-50 ... 90 °C
Ambient temperature with flexible cable installation	-40 ... 90 °C
CE 符號 (參見符合的標準)	根據 EU 低電壓設備指導原則 in accordance with EU RoHS directive
UKCA marking (see declaration of conformity)	To UK instructions for electrical equipment To UK RoHS instructions
PWIS conformity	VDMA24364-B2-L
材料備註	符合 RoHS
污染程度	3
耐腐蝕等級 CRC	0 - No corrosion stress
Material cable sheath	TPE-U(PUR)
電纜外套顏色	橙色
Material insulation	TPE-E