

# dosing needle set

## VAVN-N-A1.6-03-60-V-V1-P10

料號: 8104297

FESTO



### 技術參數

特性	值
容器尺寸	10
Dosing needle outside diameter	1.6 mm
Length of dosing needle	60 mm
Nominal width of dosing needle	0.3 mm
Dosing needle version	With tapering
耐腐蝕等級 CRC	3 - High corrosion stress
PWIS conformity	VDMA24364 zone III
Food-safe	See Supplementary material information
Fluid connection	Terminal connection
介質	流體介質 氣態介質
Note on the medium	Observe resistance of materials that come into contact with media Maximum particle size: 5 µm
Operating pressure MPa	0 ... 0.4 MPa
操作壓力	0 ... 4 bar
標準額定流量	1.32 l/min
Information on standard nominal flow rate	In case of a pressure drop of 1 -> 0 bar (gaseous media)
流量 Kv	0.003 m3/h
Information on flow rate Kv	For water as medium
介質溫度	5 ... 60 °C
環境溫度	5 ... 60 °C
儲藏溫度	-20 ... 70 °C
裝配位置	任何
產品重量	8.1 g
材料備註	符合 RoHS
Material of dosing needle	高合金鋼, 耐腐蝕
Material number of dosing needle	1.4404
材料與介質接觸	高合金鋼, 耐腐蝕