


端板

CPX-AP-A-EPR

料號: 8112477

FESTO



技術參數

特性	值
尺寸 寬(W) x 長(L) x 高(H)	(installation dimensions) 30,4 mm x 117,2 mm x 53,6 mm
網柵尺寸	50.1 mm
安裝類型	Direct mounting via through-holes On H-rail with accessories Via through-hole for M5 screw Via through-hole for M6 screw
產品重量	116 g
裝配位置	Any, on H-rail: horizontal
環境溫度	-20 ... 50 °C
Note on ambient temperature	Note ambient temperature derating according to IEC 61131-2:2017
儲藏溫度	-20 ... 70 °C
相對空氣濕度	5 - 95 % 非冷凝
Nominal altitude of use	<= 2000 m ASL (> 79,5 kPa)
Max. installation height	3,500 m
Note on max. installation height	> 2000 m ASL (< 79,5 kPa) Note ambient temperature derating according to IEC 61131-2:2017
耐腐蝕等級 CRC	1 - Low corrosion stress
耐振動	傳送應用測試在安全等級 2 符合 FN 942017-4 及 EN 60068-2-6
Note on vibration resistance	SG1 on H-rail SG2 on direct mounting 傳送應用測試在安全等級 1 符合 FN 942017-4 及 EN 60068-2-6
耐衝擊	Shock test with severity level 2 in accordance with FN 942017-5 and EN 60068-2-27
Note on shock resistance	30 g/11 ms to EN 60068-2-27 SG1 on H-rail SG2 on direct mounting Shock test with severity level 1 in accordance with FN 942017-5 and EN 60068-2-27
安全等級	III
Overvoltage category	II
PWIS conformity	VDMA24364-B2-L
材料備註	符合 RoHS 不含鹵素 Free of phosphoric acid ester
Material end plate	Die-cast aluminium, coated
Material screws	Steel, nickel-plated
Material seals	PU 泡沫