

安全夾
NPAP-QE-S-Q4-P10
料號: 8113228

FESTO



技術參數

特性	值
容器尺寸	10
裝配位置	任何
Operating pressure for entire temperature range	-0.095 ... 0.8 MPa
操作壓力的完整溫度範圍	-0.95 ... 8 bar
Operating pressure for entire temperature range	-13.775 ... 116 psi
耐腐蝕等級 CRC	1 - Low corrosion stress
PWIS conformity	VDMA24364 zone III
無塵室等級	This product is a static object, active particle generation is not possible when used correctly. Clean product before using it in a cleanroom environment and ensure it is installed correctly.
環境溫度	-5 ... 60 °C
產品重量	0.06 g
氣壓連接	For tubing outside diameter 4 mm
材料備註	符合 RoHS