

**雙氣嘴**  
**NPFC-DS-G14-G12-M**  
料號: 8142587

FESTO



**技術參數**

特性	值
Material threaded fitting	Nickel-plated brass
容器尺寸	10
操作壓力	-0.95 ... 10 bar
操作介質	壓縮空氣符合 ISO8573-1:2010 [7:8:4]
耐腐蝕等級 CRC	1 - Low corrosion stress
PWIS conformity	VDMA24364-B2-L
環境溫度	-10 ... 60 °C
Nominal tightening torque, pneumatic connection 1	47.9 Nm
Nominal tightening torque, pneumatic connection 2	9.05 Nm
額定擰緊扭矩公差	± 20 %
產品重量	34.4 g
氣壓連接, 氣口 1	G1/2
氣壓連接, 氣口 2	G1/4
材料備註	符合 RoHS
Material seals	PVC