

接頭組件 DADG-AK-G8-20-40

料號: 8152390

FESTO



技術參數

特性	值
尺寸	20
行程	40 mm
Operating pressure MPa	0.1 ... 0.8 MPa
操作壓力	1 ... 8 bar
Operating pressure	14.5 ... 116 psi
操作介質	壓縮空氣符合 ISO8573-1:2010 [7:4:4]
耐腐蝕等級 CRC	1 - Low corrosion stress
PWIS conformity	VDMA24364-B1/B2-L
環境溫度	-10 ... 60 °C
最大緊固扭矩	3 Nm
Tightening torque tolerance	± 10 %
最大的緊固扭矩, 氣接口 1	3 Nm
產品重量	37.5 g
氣壓連接	G1/8
Material adapter	環氧樹脂
Material seals	FPM
Material screws	Coated steel