



- Air gun with lever operation
- Sturdy aluminium design
- Interchangeable nozzles

Air guns LBP

Technical data

FESTO

- Sturdy aluminium design
- Interchangeable nozzles


 - Operating pressure
0 ... 10 bar



General technical data	
Exhaust function	Non-metered blowing
Pneumatic connection	Female thread G $\frac{1}{4}$
Operating pressure [bar]	0 ... 10
Standard nominal flow rate [l/min]	120 at 6 bar
Noise level [dB (A)]	90 at 6 bar
Material	Aluminium
Ambient temperature [°C]	-10 ... +50
Weights [g]	240

- | - Note: This product conforms with the ISO 1179-1 standard and the ISO 228-1 standard.

Dimensions



Note
This air gun has no pressure regulating valve.

Note
Compressed air guns must not be pointed at people.

1 Sealing surface

- | - Note: This product conforms with the ISO 1179-1 standard and the ISO 228-1 standard.

Ordering data		
Pneumatic connection	Part No.	Type
G $\frac{1}{4}$	35 528	LBP- $\frac{1}{4}$

Low consumption air guns LSP

Technical data

- Fine, infinitely variable, lever operated flow metering
- Interchangeable nozzles

 - Operating pressure
0 ... 10 bar



General technical data	
Exhaust function	Metered blowing
Pneumatic connection	Female thread G $\frac{1}{4}$
Operating pressure [bar]	0 ... 10
Standard nominal flow rate [l/min]	120 at 6 bar
Noise level [dB (A)]	90 at 6 bar
Material	Polyamide
Ambient temperature [°C]	-10 ... +50
Weights [g]	125

-||- Note: This product conforms with the ISO 1179-1 standard and the ISO 228-1 standard.

Dimensions

Note
This air gun has no pressure regulating valve.

Note
Compressed air guns must not be pointed at people.

1 Sealing surface

-||- Note: This product conforms with the ISO 1179-1 standard and the ISO 228-1 standard.

Ordering data	
Pneumatic connection	Part No. Type
G $\frac{1}{4}$	184 318 LSP- $\frac{1}{4}$ -C


Air guns

Accessories

Air gun nozzle LPZ-SD with safety shield

- Accurate, high power air jet with protective air shield for chips and dust
- Low noise level

Material:
Aluminium




Ordering data		
	Part No.	Type
Air gun nozzle with protective air shield	184 321	LPZ-SD

Air gun nozzle LPZ-LD with noise reduction

- Powerful, focused air jet
- For blowing out, drying and cooling large surfaces
- Low noise level

Material:
Chrome plated die-cast zinc/
aluminium




Ordering data		
	Part No.	Type
Air gun nozzle with noise reduction	184 322	LPZ-LD

Air gun nozzle LPZ-RG-150 with straight tube

- Accurate, high power air jet for difficult to access locations
- 150 mm long
- Nozzle \varnothing 2 mm

Material:
Brass



Ordering data		
	Part No.	Type
Air gun nozzle with straight tube	184 320	LPZ-RG-150


Air guns

Accessories

Air gun nozzle LPZ-RB-150 with elbow tube

- Accurate, high power air jet for difficult to access locations
- 150 mm long
- Nozzle \varnothing 2 mm
- 360° rotatable

Material:
Brass



Ordering data		Part No.	Type
Air gun nozzle with elbow tube		184 319	LPZ-RB-150

Nominal flow rate q_n with fully actuated lever as a function of the output pressure p

measured using low consumption air gun LSP-1/4-C

