


Plastic tubing PU

FESTO



Characteristics

At a glance

Highly flexible plastic tubing that is characterised by excellent resistance to abrasion and kinking.

- Standard I.D.
- Polyurethane with fabric
- Operating media compressed air, vacuum (PU-13)

Additional documents

[Link](#)  [pu](#)



The additional document ID-TUBING-ADD contains further information on operating conditions and measuring methods.

Datasheet

General technical data

Inside diameter	9 mm	13 mm
Outside diameter	11.6 mm	17.6 mm
Pneumatic connection	For barbed fitting inside diameter of 9 mm with union nut	For barbed fitting inside diameter of 13 mm with union nut
Flow-relevant bending radius	76 mm	83 mm

Operating and environmental conditions

Inside diameter	9 mm	13 mm
Operating pressure complete temperature range	0 ... 10 bar	-0.95 ... 10 bar
Operating medium	Compressed air to ISO 8573-1:2010 [7:::]	
Note on operating and pilot medium	Lubricated operation possible	
Ambient temperature	-35 ... 60°C	

Materials

Inside diameter	9 mm	13 mm
Shore hardness	A 91 +/-3	A 86 +/-3
Material tubing	TPE-U(PU)	
Note on materials	RoHS-compliant	
LABS (PWIS) conformity	VDMA24364-B1/B2-L	

Ordering data

Ordering data						
	Inside diameter	Outside diameter	Colour	Product weight according to length ¹⁾	Part no.	Type
	9 mm	11.6 mm	Black	0.056 kg/m	12134	PU-9-SW
	13 mm	17.6 mm		0.133 kg/m	12133	PU-13-SW

1) Packaging unit: 50 m

Accessories

Quick connector CK

	Pneumatic connection, port 1	Pneumatic connection, port 2	Nominal size	Size of pack	Part no.	Type
	Male thread G1/4	For barbed fitting inside diameter of 9 mm with nut	8 mm	10	2031	CK-1/4-PK-9
	Male thread G3/8	For barbed fitting I.D. 13 mm with nut	11.7 mm		4097	CK-3/8-PK-13