

# Plug CAMF-B-M25-G4

Part number: 555676

FESTO



## Data sheet

Feature	Value
Additional functions	Mounting to prevent loss
Mounting position	optional
Nominal operating voltage DC	24 V
Operational voltage range AC	160 V
Permissible current load	1 A
Degree of protection	IP65 To IEC 60529
LABS (PWIS) conformity	VDMA24364-B2-L
Note on materials	RoHS-compliant
Corrosion resistance class CRC	0 - No corrosion stress